



Model 160

Screening Audiometer

- Hearing level printouts with portable printer
- Compact and easy to use
- Reduced test time
- Pure tone, continuous, pulsed and warble tones
- Totally portable
- 10 test frequencies
- -10 to 100 dBHL range
- Optional carrying case for mobile use

The **Amplivox 160** is designed to improve results recording by producing an audiogram printout when used with the specified compact printer. It is the ideal audiometer for primary care groups, surgeries and industry. It offers a comprehensive air conduction threshold facility at a cost-effective price.

Improved Use

A reduced test time and improved patient concentration is made possible by the threshold retention function. Test results can be recorded during the test. Upon test completion, results can be printed with the optional printer, saved in memory for later use or recorded manually.

Ergonomic Design

Laid out in an ergonomic manner, the control panel is clear, easy to read and very easy to use with all settings and results displayed on the integral display.

The **Amplivox 160** is designed and manufactured to conform with relevant audiometric and safety standards.

Totally Portable

Lightweight and compact, the **Amplivox 160** is totally portable and is ideal for both desktop and mobile needs.

The 160 can also be supplied with the optional battery power function in addition to mains power if required.

